




## **Laminar Flow Vertical Specifications**

-10" plexiglass sash

Adjustable sliding sash rail on/off switches, cuit brakers water/filter guage,



Optional accessory-2

Work surface

15 or 20 Amp outlets-

## vertical lam flow 30 x 72 x 90" h

30" spacing from top of work surface to bottom of filter frame

(2) 36" x 22 FFU filter motor unit, 99.99% x 3" hepa filters, 15 amp power

(2) Pre filters

Plexiglass side panels

Steel rear panel

(2) outlets in rear panel

15Amp power cord terminated on side of FFU

LED under counter light

(2) On/off switches, 1) for accessories, 1 for FFU's

2 x 2 tubular frame

Work surface

Steel skirt around FFU units

32" h work surface hgt

fixed sash and is optional

30" opening from top of work surface to under side of filters

Power cord on side of unit

Inside dimension of work surface, deduct 4"overall from side

